

homogenizer gauges DS 4" (100mm)





These instruments are designed for homogenizer machines and are built according to standard n. 74-06 of 3-A organization (Sanitary Standards Symbol Administrative Council). The absence of interstices and the mirror finishing of the components assure the best hygiene. The process connection is a special diaphragm seal integrally built with the pressure gauge. To reduce the effects of severe operating conditions like vibrations and pulsations, the instruments can be liquid filled. These types of sensors are intended for Manual (COP) Cleaning.

1.OM.2 - Fillable model

Design: 74-06 SSI; EN837-1.

Safety designation: S1 as per EN 837-2.

Ranges: from 0...2000 psi to 0...15000 psi; (from 0...160 bar to 0...1600

bar or equivalent units).

Accuracy: class 1,6 as per EN 837-1.

Ambient temperature: -13...+149 °F (-25...+65 °C). **Process temperature:** -4...+248 °F (-20...+120 °C).

Max 302°F (150 °C) for 1 hour during sterilization (S.I.P)1.

Working pressure (referred to the full scale value): max 75%.

Over pressure limit: not available. Seal fill: oil for food service (FDA).

Protection degree: IP 67 as per EN 60529/IEC 529.

Process connection: AISI 316L st.st. with finishing Ra \leq 0,8 μ m (welded

parts included).

Diaphragm: AISI 316L **Welding:** AISI 316L TIG.

Flange and screw nut: AISI 316 st.st.

Case: stainless steel.

Ring: stainless steel, bayonet lock.

Elastic element: AISI 316L st.st. spiral form.

Window: tempered glass. Movement: stainless steel.

Dial: aluminium, white with black markings.

Pointer: aluminium black anodized.

1.OM.3 - Filled model

Case filling liquid: glycerine 99,5% (USP, E.P. and F.U.) for food

service.

Ambient temperature: +59...+149 °F (+15...+65 °C).

Other features: as fillable model.

1) S.I.P. = Steamed In Place

| RANGES | bar | bar ext. |
|-----------|-----|----------|
| | | psi int. |
| 0160 | • | • |
| 0250 | • | • |
| 0400 | • | • |
| 0600 | • | • |
| 01000 | • | • |
| 01600 (1) | • | • |


| RANGES | psi |
|--------|-----|
| 02000 | • |
| 03000 | • |
| 04000 | • |
| 05000 | • |
| 06000 | • |
| 010000 | • |
| 015000 | • |
| | |

(1) available for some connections only





IN ORDER TO IMPROVE THEIR PRODUCTION, MESSEN. NUOVA FIMA RESERVE THE RIGHTTO THEMSELIVES TO MAKE ALL THE MODIFICATIONS THAT THEY DEEM INDISPENSABLE AT ANY TIME. UPDATED DATA-SHEETS ARE AVAILABLE ON SITE: WWW. ILLOYA FIME TO THEMSELIVES TO MAKE ALL THE MODIFICATIONS THAT THEY DEEM INDISPENSABLE AT ANY TIME. UPDATED DATA-SHEETS ARE AVAILABLE ON SITE: WWW. ILLOYA FIME TO THEMSELIVES TO MAKE ALL THE MODIFICATIONS.




| 1 4 1 | ø d ₁ |
|-------|------------------|
| | |
| -1 c | |
| | |
| | øD |
| | |
| | |
| | |
| | |

A - LOWER CONNECTION

335 - SA 335 (with flange)

| a | b | С | d | d ₁ | h |
|-------|--------|-------|---------|----------------|---------|
| 0.51" | 1.90" | 0.62" | 4.35" | 3.97" | 6.08" |
| (13) | (48,5) | (16) | (110,6) | (101) | (154,5) |

167 - SA 167



Customer drawing process connection available on request

| Drawing | ØD | Ø M | Ø A | Ø B | Н | S | G | L | E | Ø F | I | R | Q | Weight |
|---------|-------|--------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-----------|
| SA 335 | 0.86" | 0.95" | | 1.30" | 3.38" | 0.25" | | 0.51" | 3.74" | 0.70" | 2.36" | 1.10" | 1.77" | 4.01 lbs |
| 311 333 | (22) | (23,5) | | (33,3) | (86) | (6,5) | | (13) | (95) | (18) | (60) | (28) | (45) | (1,82 kg) |
| SA 167 | 1.22" | 0.95" | 1.33" | 1.47" | 3.38" | 0.43" | 0.04" | 0.39" | | | | | | 2.84 lbs |
| 3A 107 | (31) | (23,5) | (34) | (37,5) | (86) | (11) | (1 | (10) | | | | | | (1,29 kg) |

dimensions: inches (mm)

OPTIONS

| Model | Fillable | Filled | | |
|---|-------------------------------|--------------------------------------|--|--|
| \$35 - Connection as per SA 335, without flange | • | • | | |
| 2D1 - ATEX II 2GD c version | See the ATEX datasheet for | pressure gauges technical details | | |
| L22 - Maximum pointer IP 65 on plexiglas window (1) | • | • | | |
| T32 - Safety glass window | • | • | | |
| TPC - Polycarbonate window | • | * | | |

(1) Accuracy refers to the area free from the maximum pointer action.

"HOW TO ORDER" SEQUENCE

2

3

Section / Model / Case / Mounting / Diameter / Range / Process connection / Options

 \mathbf{OM} 1

NUOVA FIMA USA Inc.

 \mathbf{E}

167

335

S35 2D1...TPC

Copyright © Nuova Fima srl. All rights reserved. Any part of this publication should not be reproduced without a written Nuova Fima's srl approval